

High-Energy X-ray Line-Scan Camera Series

XIH8800 Series

The X-Scan Imaging XIH8800 series of linear array x-ray cameras offers high performance for high-energy x-ray and gamma-ray scanning applications in a compact form factor. A heavy-metal housing shields diode arrays and electronics ensuring long-life reliability under extreme radiation conditions. A wide selection of scintillation material converts high-energy photons into visible light, fiber optics convey the visible light to a shielded, off-axis CMOS imaging linear diode array (LDA) while providing a wide dynamic range, optimization of sensitivity and resolution, and solid-state reliability. The close proximity of the analog-to-digital converters (ADC) to the detector chips and the use of low-voltage-differential-signal (LVDS) technology minimize interference noise. A collection of hardware for interfacing to computers and software including drivers, an intuitive application programming interface (API), and example code software expedite developments of x-ray scanning systems.

Key Features

Off-axis, fiber-optic design for high-energy reliability in a compact form factor

• 50 KeV to 15 MeV energy range

- Choice of scintillators: GOS:Tb, CsI:Tl, CWO
- Wide range of resolutions & selection of lengths
- Incorporates X-Scan Imaging's proprietary photodiode arrays
 - Selectable resolution
 - o Low noise, wide dynamic range, high sensitivity
 - High MTF
- 16-bit analog-to-digital conversion
- Supports variable scan speed with position synchronization
- Software development kit
 - o Device drivers, libraries, standard API
- GigE/Camera Link/USB3 interface

Applications

- Industrial non-destructive testing (NDT)
- Weld and corrosion inspection
- Fan-beam computed tomography (CT)



XIH8800 High-Energy X-ray Line-Scan Camera Series


Models

Model: XIH88[LLL]i						
Model series	XIH8850	XIH8801	XIH8802	XIH8804	XIH8808	XIH8816
Resolution	50 µm	0.1 mm	0.2 mm	0.4 mm	0.8 mm	1.6 mm
Number of pixels	$LLL \times 512$	$LLL \times 256$	$LLL \times 128$	$LLL \times 64$	$LLL \times 32$	$LLL \times 16$
Maximum line rate ⁱⁱ	550 Hz	1500 Hz	3 KHz	6 KHz	12 KHz	23 KHz

ⁱ Active Length is (25.6 mm \times *LLL*) where *LLL* is a multiple of 6 and *LLL* \ge 12 (minimum length is 308 mm and no maximum length limit).

Setup

The XIH8800 series camera system includes a camera unit, a software development kit, power adapter and cabling. The frame-grabber to be installed in the computer is provided optionally. The objects to be scanned should be passed between the x-ray source and the camera.



Information furnished by X-Scan Imaging is believed to be accurate and reliable. However, no responsibility is assumed by X-Scan Imaging Corporation for its use. Users are responsible for their products and applications using X-Scan Imaging components. To minimize the risks associated with users' products and applications, users should provide adequate design and operating safeguards. No responsibility is assumed by X-Scan Imaging Corporation for any infringements of patents or other rights of third parties that may result from the use of the information. No license is granted by implication or otherwise under any patent or patent rights of X-Scan Imaging Corporation.

Camera Link® is a registered trademark of the Automated Imaging Association, Ann Arbor, Mich.

107 Bonaventura Dr., San Jose, CA 95134, U.S.A. Fax: +1 408 432 9889

www.x-scanimaging.com

Tel: +1 408 432 9888

ii The maximum line rate is available for *LLL*≤18 (461 mm). Also depending in scintillator choice, image quality may be degraded at line rates greater than 1 KHz.